

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 10/07mm**


## Order data

Order number	261354 10/07
GTIN	4045197948045
Item class	21T

## Technical description

Clamping height $L_2$	9 mm
ISO code toolholder	A10H SV95CR/L07
Head length $L_1$	22 mm
Overall length $L$	100 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Pack of insert screws	269028 27
Setting angle $\kappa$	95 degrees
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Centre offset $L_3$	7 mm
Neck width $L_4$	6.8 mm
Usable depth $T$	5 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200