

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	261354 12/07
GTIN	4045197948052
Item class	21T

Technical description

Insert size	7 mm
suitable indexable insert	VC.. 0702..
Setting angle κ	95 degrees
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Pack of insert screws	269028 27
ISO code toolholder	A12K SV95CR/L07
Centre offset L_3	9 mm
Overall length L	125 mm
Clamping height L_2	11 mm
Head length L_1	28 mm
Neck width L_4	9 mm
Usable depth T	6 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200