

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 16/07mm**


## Order data

Order number	261354 16/07
GTIN	4045197948069
Item class	21T

## Technical description

Head length $L_1$	36 mm
Neck width $L_4$	12.9 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Centre offset $L_3$	11 mm
Overall length $L$	150 mm
Clamping height $L_2$	15 mm
Insert size	7 mm
Setting angle $\kappa$	95 degrees
Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
ISO code toolholder	A16M SV95CR/L07
Usable depth $T$	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200