

KÄRCHER**High pressure cleaner unheated, Manufacturer's designation: HD615MPLUS****Order data**

Order number	078571 HD615MPLUS
GTIN	4054278359960
Item class	07C

Description**Version:**

Mobile high pressure jet cleaner with AC motor. Cleaner has **pressure switch control**, anti-kink system, high-pressure hose that can be rotated under pressure and rotatable stainless steel tubular jet. Sturdy 3-piston axial pump with brass cylinder head. Water infeed of brass. Maximum infeed temperature 60 °C.

The **EASY! Force** high-pressure gun uses the reaction force of the high-pressure jets and therefore reduces the force the user applies to hold the gun. Ensures completely new and non-fatiguing comfortable working. Improved fully ceramic valve. Integral EASY!Lock connection system. Permits quick and easy fitting of accessories (such as nozzles, mild steel pipes) with uniform connections.

· **3-piston axial pump with hardened stainless steel pistons.**

Supplied with:

10 m high premium pressure hose, EASY!Force gun with softgrip inlay, stainless steel tubular jet 840 mm, power nozzle and dirt abradar.

Technical description

Weight	30 kg
--------	-------

Pumped volume	560 l/h
Mains supply fuse	16 A
Manufacturer's designation	HD 6/15 M Plus *EU
Power consumption	3100 W
Working pressure	150 bar
Power supply	Mains operated
Type of product	High-pressure cleaner