

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 8/05mm


Order data

Order number	261355 8/05
GTIN	4045197948076
Item class	21T

Technical description

Centre offset L_3	5 mm
Overall length L	80 mm
Insert size	5 mm
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Pack of insert screws	269028 26
Neck width L_4	6 mm
suitable indexable insert	VC.. 0501..
ISO code toolholder	A08F SV95CR/L05
Clamping height L_2	7.5 mm
Setting angle κ	95 degrees
Head length L_1	15 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200