

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 16/07mm

Order data

Order number	261355 16/07
GTIN	4045197948304
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Clamping height L_2	15 mm
suitable indexable insert	VC.. 0702..
Head length L_1	36 mm
Neck width L_4	12.9 mm
Pack of insert screws	269028 27
ISO code toolholder	A16M SV95CR/L07
Centre offset L_3	11 mm
Setting angle κ	95 degrees
Insert size	7 mm
Overall length L	150 mm
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200