

Garant**Screw-on toolholder, right-hand, Shank size / insert size: 8/07mm****Order data**

Order number	261306 8/07
GTIN	4045197948311
Item class	21T

Technical description

Overall length L	60 mm
Head length L ₁	15 mm
Shank size	8 mm
suitable indexable insert	VC.. 0702..
Insert size	7 mm
Pack of insert screws	269028 27
ISO code toolholder	SVLCR/L 0808D07
Functional width L ₄	10 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
