

Garant**Screw-on toolholder, right-hand, Shank size / insert size: 10/07mm****Order data**

Order number	261306 10/07
GTIN	4045197948328
Item class	21T

Technical description

Overall length L	70 mm
Insert size	7 mm
Functional width L ₄	12 mm
Head length L ₁	15 mm
ISO code toolholder	SVLCR/L 1010E07
Pack of insert screws	269028 27
Shank size	10 mm
suitable indexable insert	VC.. 0702..
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
