

**Garant****Screw-on toolholder, right-hand, Shank size / insert size: 12/07mm****Order data**

Order number	261306 12/07
GTIN	4045197948335
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	16 mm
Pack of insert screws	269028 27
Shank size	12 mm
ISO code toolholder	SVLCR/L 1212F07
Overall length L	80 mm
Head length L <sub>1</sub>	18 mm
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200

---