

Garant**Screw-on toolholder, left-hand, Shank size / insert size: 12/07mm****Order data**

Order number	261307 12/07
GTIN	4045197948366
Item class	21T

Technical description

Head length L_1	18 mm
ISO code toolholder	SVLCR/L 1212F07
Insert size	7 mm
Shank size	12 mm
Overall length L	80 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 27
Functional width L_4	16 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
