

**Garant**
**Screw-on toolholder, neutral, Shank / insert size: 10/07mm**

**Order data**

Order number	261317 10/07
GTIN	4045197948380
Item class	21T

**Technical description**

Shank size	10 mm
Pack of insert screws	269028 27
Overall length L neutral holders	150 mm
suitable indexable insert	VC.. 0702..
Insert size	7 mm
ISO code toolholder	SVVCN 1010M07
Overhang L <sub>1</sub> neutral holders	15 mm
Functional width L <sub>4</sub> neutral holders	5 mm
Series	QuickTurn
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle $\kappa$	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200