

**Garant**
**CNMM 160624, Type: HB7010-1**


### Order data

Order number	250462 HB7010-1
GTIN	4045197948434
Item class	21G

### Description

CNMM 160624 HB7010-1 Grade: HB7010-1  
 Chip breaker: SR  
 Cutting depth  $a_p$ : 2 - 10 mm  
 Feed  $f$ : 0.4 - 1.2 mm/rev.  
 Cutting speed  $v_c$  main application: 100 - 375 m/min

### Technical description

Chip breaker	SR
Grade	HB7010-1
Main application	P
Cutting conditions	continuous
Cutting depth $a_p$	2 - 10 mm
Finishing/roughing assignment	Roughing
Feed $f$	0.4 - 1.2 mm/rev.

Tool material	Carbide
Corner radius	2.4 mm
Cutting speed $v_c$ main application	100 - 375 m/min
ISO code indexable insert	CNMM 160624
Number of changes/inserts	4
Type of product	Indexable insert for turning