

Garant**SCMT 120408, Grade: HB7010-1**

Order data

Order number	260750 HB7010-1
GTIN	4045197948496
Item class	21G

Description

SCMT 120408 HB7010-1 Corner radius: 0.8 mm
Grade: HB7010-1
Chip breaker: SS
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.05 - 0.2 mm/rev.
Cutting speed v_c main application: 150 - 500 m/min

Technical description

Grade	HB7010-1
Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	150 - 500 m/min
Tool material	Carbide
Chip breaker	SS
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm

Feed f	0.05 - 0.2 mm/rev.
Main application	P
Cutting conditions	continuous
ISO code indexable insert	SCMT 120408
Number of changes/inserts	4
Type of product	Indexable insert for turning