



Tape measure Vario, accuracy class 1, Tape length: 10m



Order data

Order number	462090 10
GTIN	4007368114918
Item class	46M

Description

Version:

A particularly lightweight and handy tape measure for professional use. Body of glass fibre-reinforced polyamide. **With push button for tape lock and automatic return.** Plain bearing of special TRIBOCOMP® material with Teflon ensures **smooth gliding** and exceptionally easy running. Innovative dampers of special rubber absorb the reaction energy and protect the wrist. A special clear lacquer protects the tape against wear. The **additional anti-glare correction** ensures clear visibility under all light conditions.

Technical description

Body length	76 mm
Body height	75 mm
Body width	32 mm
Tape width	19 mm
Standard	EG I
Calibration	G1
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 10 m

026240 10