

**Garant****Tape measure, Length: 3 m****Order data**

Order number	461900 3
GTIN	4045197949264
Item class	41H

**Description****Version:**

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return.

For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**.

Plain bearings with Teflon ensure smooth action and exceptionally easy running.

**Innovative dampers** of special rubber absorb the reaction energy and protect the wrist.

**Aluminium profile inserted** on the underside for precise standing.

A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

mm graduation

Calibration: G1

Standard: EG II

Tape width: 13 mm

Body length: 62 mm

Body width: 26 mm

Body height: 59 mm

**Technical description**

Tape width	13 mm
Band length	3 m
Body width	26 mm
Body height	59 mm
Body length	62 mm
Standard	EG II
Calibration	G1
Type of product	Locking tape measure in a frame capsule housing

## Services

Calibration Locking tape measure maximum length 5 m	016140 5
Labelling laser-etched Type	018940
5	026250 5
Calibration Tape measure maximum length 5 m	026240 5