

Garant**Tape measure mm/inch, Length: 5m**

Order data

Order number	461910 5
GTIN	4045197949301
Item class	41H

Description

Version:

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return.

For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**.

Plain bearings with Teflon ensure smooth action and exceptionally easy running.

Innovative dampers of special rubber absorb the reaction energy and protect the wrist.

Aluminium profile inserted on the underside for precise standing.

A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

mm/inch graduations

Technical description

Tape width	16 mm
Body length	70 mm
Band length	5 m
Body width	30 mm

Body height	69 mm
Standard	EG II
Calibration	G1
Reversible reading	mm / inch
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 5 m	026240 5
--	----------