

Garant**Tape measure mm/inch, Length: 2m****Order data**

Order number	461910 2
GTIN	4045197949288
Item class	41H

Description**Version:**

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return.

For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**.

Plain bearings with Teflon ensure smooth action and exceptionally easy running.

Innovative dampers of special rubber absorb the reaction energy and protect the wrist.

Aluminium profile inserted on the underside for precise standing.

A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

mm/inch graduations

Technical description

Tape width	13 mm
Band length	2 m
Body length	62 mm
Body height	59 mm
Body width	26 mm

Standard	EG II
Calibration	G1
Reversible reading	mm / inch
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 2 m	026240 2
--------------------------------------------	----------