

BMI[®]**Tape measure, Band length: 10m**

Order data

Order number	462120 10
GTIN	4007368114925
Item class	46M

Description

Version:

A particularly lightweight and handy tape measure for professional use. Body of glass fibre-reinforced polyamide. **With push button for tape lock and automatic return.** Plain bearing of special TRIBOCOMP[®] material with Teflon ensures **smooth gliding** and exceptionally easy running. Innovative dampers of special rubber absorb the reaction energy and protect the wrist. A special clear lacquer protects the tape against wear. The **additional anti-glare correction** ensures clear visibility under all light conditions.

Technical description

Body height	77 mm
Body length	78 mm
Body width	32 mm
Tape width	19 mm
Standard	EG II
Calibration	G1

Type of product

Measuring tape

Services

CalibrationTape measure maximum length 10 m

026240 10