

Garant**Light metal spirit level with magnet, Length: 800mm****Order data**

| | |
|--------------|---------------|
| Order number | 467025 800 |
| GTIN | 4045197949325 |
| Item class | 41H |

Description**Version:**

Thick-walled anodised aluminium profile with very high rigidity. Flat and Vee-form measuring faces for perfect alignment on surfaces, pipes and edges. Flush horizontal vial with magnifying effect creates distortion-free view of the vial bubble.

With **powerful permanent magnets**.

Technical description

| | |
|--------------------------------------|---------------------------|
| Number of horizontal vials | 1 |
| Error limit in normal position | 0.5 mm/m |
| Number of vertical vials | 1 |
| Error limit for overhead measurement | 0.75 mm/m |
| Length | 800 mm |
| Cross section | 24 × 55 mm |
| Magnet | Permanent magnet |
| Type of measurement face | prismatic measuring faces |
| Material of the housing | Aluminium |
| Type of product | Spirit level |