

Garant**Positioning clamping pin, Ød1×length l1: 16X25mm**

Order data

Order number	370105 16X25
GTIN	4045197943781
Item class	31E

Description

Advantage:

- Thanks to the pre-loaded spring, there is no overloading on the internal mechanism, which is thus wear resistant.
- Vibration-damping.
- Self-locking, does not work loose due to vibration.
- High repetition accuracy ± 0.03 mm.
- Low installed height.
- Easy to use.

Application:

For quick clamping, fixing, adjusting, exchanging and securing of workpieces, plates, jigs etc.

Material:

Through-hardened steel, burnished

Technical description

Holding force	5 kN
Length l ₂	13.6 mm

Length l_3	10 mm
Width across flats 2	6 mm
Width across flats 1	30 mm
for clamping plates ± 0.05	20 mm
Type of product	Clamping studs