

Garant**Positioning clamping pin, Ød1×length l1: 20X30mm****Order data**

Order number	370105 20X30
--------------	--------------

GTIN	4045197949417
------	---------------

Item class	31E
------------	-----

Description**Advantage:**

- Thanks to the pre-loaded spring, there is no overloading on the internal mechanism, which is thus wear resistant.
- Vibration-damping.
- Self-locking, does not work loose due to vibration.
- High repetition accuracy ± 0.03 mm.
- Low installed height.
- Easy to use.

Application:

For quick clamping, fixing, adjusting, exchanging and securing of workpieces, plates, jigs etc.

Material:

Through-hardened steel, burnished

Technical description

Width across flats 2	6 mm
----------------------	------

Length l ₂	13.6 mm
-----------------------	---------

Width across flats 1	38 mm
Length l ₃	10 mm
Holding force	6 kN
for clamping plates ±0.05	25 mm
Type of product	Clamping studs