

Garant
Digital caliper IP54 with data output, Measuring range: 200mm

Order data

Order number	412680 200
GTIN	4045197949356
Item class	41A

Description
Version:

Digital calipers to IP54 with data output. **Easy-to-read, high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 20 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. With preset (dimension selection in advance). **Ergonomic housing with easy-grip Haptoprene component.** The measuring faces are precision-lapped.

Advantage:

- **Ergonomic housing with easy-grip Haptoprene component.**
- **Long battery life.**
- **Large high-contrast LCD display with 11.5 mm character height.**
- **New modern design.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948, keyboard interface No. 498963

Spare part:

Data output cap No. 412237 size D, battery holder No. 412237 size B.

Technical description

Number of batteries contained	1
Measuring range	0 - 200 mm

Standard	ISO 13385
Reversible reading	mm / inch
Scale divisions	0.0005 in
Scale divisions	0.01 mm
Calibration	A1
Depth gauge	rectangular 3.7×1.3
Jaw length	50 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 54
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Connection cable Type USB2	498948 USB2
Connection cable Type R2	498948 R2
Keyboard interface USB Type G2	498963 G2

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412236
Cover for digital calipers Type D	412237 D
Cover for digital calipers Type B	412237 B