

Garant**Digital caliper IP54 with data output, Measuring range: 300mm****Order data**

Order number	412680 300
GTIN	4045197949363
Item class	41A

Description**Version:**

Digital calipers to IP54 with data output. **Easy-to-read, high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 20 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. With preset (dimension selection in advance). **Ergonomic housing with easy-grip Haptoprene component.** The measuring faces are precision-lapped. without depth gauge.

Advantage:

- **Ergonomic housing with easy-grip Haptoprene component.**
- **Long battery life.**
- **Large high-contrast LCD display with 11.5 mm character height.**
- **New modern design.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948, keyboard interface No. 498963

Spare part:

Data output cap No. 412237 size D, battery holder No. 412237 size B.

Technical description

Jaw length	64 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032

Calibration	A1
Standard	ISO 13385
Number of batteries contained	1
Scale divisions	0.0005 in
Measuring range	0 - 300 mm
Reversible reading	mm / inch
Scale divisions	0.01 mm
IP Index of Protection	IP 54
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Connection cable Type R2	498948 R2
Connection cable Type USB2	498948 USB2
Plastic case Type MS300	412470 MS300
Button cell / special battery Battery type CR2032	081560 CR2032

Keyboard interfaceUSB Type G2	498963 G2
Screw for depth gauge holder	412236
Cover for digital calipers Type B	412237 B
Cover for digital calipers Type D	412237 D