

Garant

Digital caliper IP54 with rod type depth gauge and data output, Measuring range: 150mm



Order data

Order number	412682 150
GTIN	4045197949370
Item class	41A

Description

Version:

Digital calipers to IP54 with data output. **Easy-to-read, high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 20 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. With preset (dimension selection in advance). **Ergonomic housing with easy-grip Haptoprene component.** The measuring faces are precision-lapped.

Advantage:

- **Ergonomic housing with easy-grip Haptoprene component.**
- **Long battery life.**
- **Large high-contrast LCD display with 11.5 mm character height.**
- **New modern design.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948, keyboard interface No. 498963

Spare part:

Data output cap No. 412237 size D, battery holder No. 412237 size B.

Technical description

Scale divisions	0.0005 in
Standard	ISO 13385
Article no of the battery / rechargeable battery fitted	081560 CR2032
Depth gauge	Ø 1.6
Reversible reading	mm / inch
Measuring range	0 - 150 mm
Number of batteries contained	1
Calibration	A1
Jaw length	40 mm
Scale divisions	0.01 mm
IP Index of Protection	IP 54
Power supply	Battery-powered
Measurement deviation E MPE	± 0.02 mm
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------

Connection cable Type USB2	498948 USB2
Connection cable Type R2	498948 R2
Keyboard interfaceUSB Type G2	498963 G2
Screw for depth gauge holder	412236
Cover for digital calipers Type D	412237 D
Cover for digital calipers Type B	412237 B