

Garant
Digital caliper IP67 with data output, Measuring range: 300mm

Order data

Order number	412690 300
GTIN	4045197949707
Item class	41A

Description
Version:

Digital calipers to IP67 with data output. **Easy-to-read, high-contrast LCD display with 11.5mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 20 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point.

2-component body with **easy-grip Haptoprene surface.** The calipers are resistant to water, coolant, oil, and dust – even when fitted with a data cable. The measuring faces are precision-lapped. With preset (dimension selection in advance). without depth gauge

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948, keyboard interface No. 498963.

Spare part:

Data output cap No. 412237 size D, battery holder No. 412237 size B.

Technical description

Standard	ISO 13385
Measuring range	0 - 300 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Scale divisions	0.01 mm

Reversible reading	mm / inch
Jaw length	64 mm
Scale divisions	0.0005 in
Number of batteries contained	1
Calibration	A1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Interface	USB interface
Interface	RS232C interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300
CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Keyboard interfaceUSB Type G2	498963 G2
Screw for depth gauge holder	412236
Cover for digital calipers Type B	412237 B
Cover for digital calipers Type D	412237 D
Type SPRING	412240 SPRING