


HOLEX CleverDrill HSS jobber drill, uncoated, Ø DC h8: 5,4 mm

Order data

Order number	113005 5,4
GTIN	4045197952233
Item class	12B

Description
Version:

Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Through-coolant: no

Standard: DIN 1897

Tolerance nominal Ø: h8

Point angle: 130 degrees

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 19.9 mm

Flute length L_c : 28 mm

Overall length L: 66 mm

Shank Ø D_s : 5.4 mm

Feed f in steel < 750 N/mm²: 0.08 mm/rev.

Technical description

Feed f in steel < 750 N/mm ²	0.08 mm/rev.
Overall length L	66 mm
recommended maximum drilling depth L_2	19.9 mm
Shank Ø D_s	5.4 mm
Tolerance nominal Ø	h8
Flute length L_c	28 mm
Standard	DIN 1897

Nominal $\varnothing D_c$	5.4 mm
Number of cutting edges Z	2
Point angle	130 degrees
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Shank	Plain shank
Through-coolant	no
Colour ring	without
Type of product	Jobber drill