


HOLEX CleverDrill HSS jobber drill, uncoated, Ø DC h8: 9 mm

Order data

Order number	113005 9
GTIN	4045197952592
Item class	12B

Description
Version:

Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Through-coolant: no

Standard: DIN 1897

Tolerance nominal Ø: h8

Point angle: 130 degrees

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 26.5 mm

Flute length L_c : 40 mm

Overall length L: 84 mm

Shank Ø D_s : 9 mm

Feed f in steel < 750 N/mm²: 0.1 mm/rev.

Technical description

Tolerance nominal Ø	h8
Shank Ø D_s	9 mm
Nominal Ø D_c	9 mm
recommended maximum drilling depth L_2	26.5 mm
Standard	DIN 1897

Flute length L_c	40 mm
Number of cutting edges Z	2
Overall length L	84 mm
Feed f in steel < 750 N/mm ²	0.1 mm/rev.
Point angle	130 degrees
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Shank	Plain shank
Through-coolant	no
Colour ring	without
Type of product	Jobber drill