


HOLEX CleverDrill HSS jobber drill, uncoated, Ø DC h8: 9,9 mm

Order data

Order number	113005 9,9
GTIN	4045197952684
Item class	12B

Description
Version:

Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Through-coolant: no

Standard: DIN 1897

Tolerance nominal Ø: h8

Point angle: 130 degrees

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 28.15 mm

Flute length L_c : 43 mm

Overall length L: 89 mm

Shank Ø D_s : 9.9 mm

Feed f in steel < 750 N/mm²: 0.1 mm/rev.

Technical description

Tolerance nominal Ø	h8
Shank Ø D_s	9.9 mm
Flute length L_c	43 mm
Standard	DIN 1897
Nominal Ø D_c	9.9 mm
Number of cutting edges Z	2
recommended maximum drilling depth L_2	28.15 mm

Feed f in steel < 750 N/mm ²	0.1 mm/rev.
Overall length L	89 mm
Point angle	130 degrees
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Shank	Plain shank
Through-coolant	no
Colour ring	without
Type of product	Jobber drill