



## HOLEX CleverDrill HSS jobber drill, uncoated, Ø DC h8: 7,5 mm



### Order data

Order number	113005 7,5
GTIN	4045197952448
Item class	12B

### Description

#### Version:

Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Through-coolant: no

Standard: DIN 1897

Tolerance nominal Ø: h8

Point angle: 130 degrees

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 22.75 mm

Flute length  $L_c$ : 34 mm

Overall length L: 74 mm

Shank Ø  $D_s$ : 7.5 mm

Feed f in steel < 750 N/mm<sup>2</sup>: 0.08 mm/rev.

### Technical description

Standard	DIN 1897
Number of cutting edges Z	2
Flute length $L_c$	34 mm
recommended maximum drilling depth $L_2$	22.75 mm
Feed f in steel < 750 N/mm <sup>2</sup>	0.08 mm/rev.
Nominal Ø $D_c$	7.5 mm
Overall length L	74 mm

Tolerance nominal $\varnothing$	h8
Shank $\varnothing D_s$	7.5 mm
Point angle	130 degrees
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Shank	Plain shank
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

---

## Accessories

HOLEX Clever Drill stub drill set HSS No. 113005, type N in a case Type 1-10

113510 1-10