


HOLEX CleverDrill HSS jobber drill, uncoated, Ø DC h8: 17,5 mm

Order data

Order number	113005 17,5
GTIN	4045197952875
Item class	12B

Description
Version:

Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Through-coolant: no

Standard: DIN 1897

Tolerance nominal Ø: h8

Point angle: 130 degrees

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 35.75 mm

Flute length L_c : 62 mm

Overall length L: 123 mm

Shank Ø D_s : 18.5 mm

Feed f in steel < 750 N/mm²: 0.2 mm/rev.

Technical description

Overall length L	123 mm
Nominal Ø D_c	17.5 mm
Flute length L_c	62 mm
Shank Ø D_s	18.5 mm
Tolerance nominal Ø	h8
Feed f in steel < 750 N/mm ²	0.2 mm/rev.
recommended maximum drilling depth L_2	35.75 mm

Number of cutting edges Z	2
Standard	DIN 1897
Point angle	130 degrees
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Shank	Plain shank
Through-coolant	no
Colour ring	without
Type of product	Jobber drill