

Garant**Horizontal toggle clamp, variable, Type: 70****Order data**

Order number	376400 70
GTIN	4045197953322
Item class	31M

Description**Version:**

With horizontal base. Completely black nickel-plated, with solid rivets. Ergonomic 2-component handle. Captive contact screw. Complete with black nickel-plated contact screw.

Advantage:

Stepless adjustment function for variations in workpiece heights. Consistently high clamping forces.

Technical description

Clamping force	3000 N
maximum clamping height	60 mm
Contact screw	M8×66 mm
automatic height adjustment S	35 mm
Type of product	Horizontal toggle clamp