

Garant**Support columns, Height: 962mm****Order data**

Order number	938000 962
GTIN	4045197680341
Item class	91W

Description**Version:**

Of sturdy sheet metal. Barrier-free working area, since no stabilising plate required. Insertion slots at 50 mm intervals on the front face, threaded sockets on the front and inner faces for holding other modules such as perforated panels, storage shelves etc. Support columns with side openings for cable routing. Supplied in pairs.

Suitable for:

Perforated sheet steel back panels 2 pc. No. 938008 or No. 938009.

Colour:

Light grey RAL 7035 **powder coated**.

Note:

- **Size 200 is suitable only for media tracks, storage shelves and Multifix rail.**
 - **When using media tracks please also order the media module No. 938002 size CUT/OUT.**
- Suitable for mounting pair of brackets.

Technical description

Depth	100 mm
Width	40 mm

Data sheet

maximum number of perforated panels	2 × No. 938008 or No. 938009
maximum load capacity	50 kg
Height	962 mm
Weight	6 kg
Series	KOMBI-filebænk
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Safety certificate	GS TÜV Süd
Type of product	Support column

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/938000-962>