

Garant
Spindle, Type: TR14I

Order data

Order number	361119 TR14I
GTIN	4045197953377
Item class	310

Description
Version:

Trapezoidal spindle for optimal force transfer.

The 5-axis vice has a modular design. The key components are the clamping modules No. 361105 – 361110, base rails No. 361115, spindle No. 361119, spindle extensions No. 361120 and the top jaws No. 361123 – 361137.

Application:

TR14 and TR16 **for external clamping**, TR14I and TR16I **for internal clamping**.

Suitable for:

Clamping modules No. 361105 – 361110.

Optional extras:

Spindle extensions No. 361120, torque wrench No. 656050 120.

Note:

Spare parts for spindles No. 361176, 361177 and 361178.

Technical description

AF ₁	10
AF ₂	27
Length L	201.1 mm
suitable for colour code	Xpent0
External Ø D	34 mm
Series	Xpent

Type of product	Spindle
-----------------	---------

Accessories

Spindle anchor, Xpent Type 0	361176 0
Spindle nut for Xpent, complete with ring Type 0	361178 0
Nut, Xpent Type 0	361177 0