

**Garant**

**GARANT Softcut® 45° high-performance indexable face mill, with bore, Ø D / number of effective cutting edges Z: 40/4mm**


**Order data**

Order number	213555 40/4
GTIN	4045197953438
Item class	210

**Description**
**Version:**

High number of cutting edges for very high productivity. Positive rake for soft cut and low power consumption. Individual tool geometry ensures very smooth cutting.

**Note:**

Use GARANT torque screwdriver TQ No. **211750 3.0** with bit No. **674252 15IP**.

**Technical description**

Number of cutting edges Z	4
suitable indexable insert	XEEW1305
suitable indexable insert	SE.T1305
Overall length $L_{tot}$	40 mm
maximum external $\varnothing D_{max}$	52.2 mm
Cutting edge $\varnothing D_c$	40 mm

Mounting bore $\varnothing$	16 mm
Pack of insert screws	219833 (15IP; 3.0 Nm)
Series	Softcut®
Shank type	with bore
Setting angle $\kappa$	45 degrees
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	Face mill

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 3,0 N·m	211750 3,0