



Vernier height gauge with horizontally adjustable scriber, Marking height: 300mm



Order data

Order number	443720 300
GTIN	4045197953445
Item class	42D

Description

Version:

Strong and sturdy base with a lapped standing surface. With measuring beam for fine adjustment, magnifying glass and locking screw. Reading 0.02 mm. Reading zero and marking scriber are adjusted with reference to the bottom of the base (marking out from "0"). Drawing dimensions can therefore be transferred directly without the risk of calculation errors. The scriber is **carbide tipped and is longitudinally adjustable by 140 mm** (e.g. where access is difficult). Slim design of the scriber for scribing in narrow slots. Ergonomic shape of the foot prevents collisions between the scriber and the hand.

Technical description

Base length	145 mm
Vernier	1/50 mm
Error limit	0.06 mm
Calibration	E1

Data sheet

Base width	105 mm
Column cross section	28×9 mm
Standard	Manufacturer's standard
Material	Stainless steel, INOX
Type of product	Height gauge and marking device

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/443720-300>