

Garant

GARANT Softcut® 45° high-performance indexable face mill, with bore, Ø D / number of effective cutting edges Z: 200/14mm



Order data

Order number	213555 200/14
GTIN	4045197953698
Item class	210

Description

Version:

High number of cutting edges for very high productivity. Positive rake for soft cut and low power consumption. Individual tool geometry ensures very smooth cutting. For arbors to DIN 2079, with 4 additional attachment holes and without internal cooling.

Note:

Use GARANT torque screwdriver TQ No. **211750 3.0** with bit No. **674252 15IP**.

Technical description

Overall length L_{tot}	63 mm
Mounting bore Ø	60 mm
Cutting edge Ø D_c	200 mm
Number of cutting edges Z	14
maximum external Ø D_{max}	212.3 mm
suitable indexable insert	SE.T1305

suitable indexable insert	XEEW1305
Pack of insert screws	219833 (15IP; 3.0 Nm)
Series	Softcut®
Shank type	with bore
Setting angle κ	45 degrees
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	Face mill

Accessories

Torque screwdriver, fixed setting set torque 3,0 N·m	211750 3,0
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP