



## ER collet chuck, HSK-A 100 A = 160, for ER collet size: 32



### Order data

Order number	305517 32
GTIN	4045197954329
Item class	32A

### Description

#### Version:

With Balluff/RFID chip bore.

- **All shanks hard turned (for smooth running!).**
- **Through bored (without adjustment screw).**
- **HSK mating faces machined.**

#### Application:

For clamping tools with plain shanks in ER collets to DIN 6499 – Form A and B.

#### Supplied with:

Coated High-Speed clamping nut.

#### Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, ER collets No. 308881 – 309434, ER chuck key No. 309680 or 613300.

### Technical description

External $\varnothing$ D	50 mm
Overhang dimension A	160 mm
Clamping range	2 - 20 mm
for ER collets	32
Adapter	HSK-A 100 A = 160
Arbor standard	ISO 12164-1

Arbor standard	DIN 69882-6
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

---

## Accessories

ER chuck key for ER collet chuck 32	309680 32
-------------------------------------	-----------