

Garant
Lever lock toolholder, left-hand, Shank / insert size: 16/12mm

Order data

Order number	251113 16/12
GTIN	4045197954459
Item class	21T

Technical description

Lever	259015 2
Head length L ₁	26 mm
Shim	259031 20
Shim punches pack	259047 2
Overall length L	100 mm
Functional width L ₄	20 mm
suitable indexable insert	SN.. 1204..
ISO code toolholder	PSSNR/L 1616H12
Insert size	12 mm
Shank size	16 mm
Shim pins pack	259044 2
Lever screw	259018 2
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500