

Garant**Tesla meter measuring device for measurement of magnetism, Type: 1****Order data**

Order number	380865 1
GTIN	4045197954565
Item class	310

Description**Version:**

- **Light and compact design. Housing protected against dirt.**
- **Automatic measuring range selection. Display either in Tesla or Gauss.**
- **Static and dynamic measurements.**
- **Magnetic pole display N/S. Zero setting.**

Application:

For measuring residual remanence, magnetic flux density and field distribution on magnetic clamping plates.

Supplied with:

Supplied with a leather case and 4 × AA batteries.

Note:

If wear occurs, the sensor No. 380866 size 1 can easily be reordered and exchanged.

Technical description

Measurement range for dynamic fields	0 - 750 mT
Measuring accuracy	± 5%
Operating temperature	0 - 40 °C
Measurement range for static fields	0 - 1500 mT

Power supply	Battery-powered
Battery type	Mignon, AA
Number of batteries contained	4
Type of product	Magnetic field measuring device

Accessories

Measurement sensors for Tesla meters for type 1	380866 1
---	----------