

STABILA **TECH digital clinometer, Type: 500****Order data**

Order number	467563 500
GTIN	4005069191252
Item class	46M

Description**Version:**

Compact and sturdy body, measuring face made of anodised aluminium. Variable attachment methods via Tee-slot, Vee-slot and rare earth magnet system. Illuminated digital display rotates when the position is inverted.

Integral warning function prevents incorrect measurements. Button locking, hold and reference function.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Includes protective case. 2× batteries No. 081561 size LR6.

Technical description

Graduations	0.01 degrees
Width	32 mm
Height	70 mm
Measuring range	360 (4×90°) degrees
Length	175 mm
Flatness tolerance	0.07 mm

Error limit of electronics module	0.05 (0°; 90°); 0.2 (1° – 89°) degrees
IP Index of Protection	IP 65
Power supply	Rechargeable battery-powered
Packaging	sturdy box
Calibration	H2
Type of product	Clinometer

Services

Calibration Engineer's level / electronic clinometer Accuracy 0,02 mm/m	026620 0,02
--	-------------

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------