

Garant**Malleable cast iron screw clamp, Jaw capacity: 250mm****Order data**

Order number	860050 250
GTIN	4045197559647
Item class	81D

Description**Version:**

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping.

Movable clamping arm **with anti-slip protection**, preventing inadvertent release of the clamp. Movable pressure pad from size 160 can be exchanged without tools.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with easy-grip Haptoprene surface and impact-resistant PP core. Surface structure is anti-slip even with wet, oily hands. With plastic protective cover on the clamping jaw.

Standard:

DIN 5117

Spare part:

Protective cap No. 860051.

Technical description

Jaw capacity	250 mm
--------------	--------

Throat	120 mm
Cross section of the slide rail	29×9 mm
Type of product	Clamp

Accessories

Pressure plate assortment 12 pieces Type 250	860051 250
--	------------