



## Malleable cast iron screw clamp, Jaw capacity: 500mm



### Order data

Order number	860000 500
GTIN	4008158011448
Item class	83J

### Description

#### Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping.

Movable clamping arm **with anti-slip protection**, preventing inadvertent release of the clamp. Movable pressure pad from size 160 can be exchanged without tools. **Without protective cap.** Clamping force of up to 7000 N.

#### Standard:

**DIN 5117**

#### Spare part:

Protective cap No. 860115.

### Technical description

Cross section of the slide rail	35×11 mm
Throat	120 mm
Jaw capacity	500 mm

Type of product	Clamp
-----------------	-------

---

## Accessories

Complete lower section for Moment screw clamps Type 500	860060 500
Pressure plate assortment 8 pieces Pressure pad Ø 37 mm	860115 37
Pair of Vario clamp attachments	862950