

SWISS TOOLS

Plain boring bar shank, Ø D – A dimension: 25-200mm**Order data**

Order number	320410 25-200
GTIN	2050001945174
Item class	36D

Description**Version:**

- For efficient turning.
- For left-hand and right-hand turning.

Application:

For mounting exchangeable cutting heads.

Note:

For suitable interchangeable heads see No. 264826 – 264827.

Technical description

Ø D	25 mm
Through-coolant	yes
Type of product	Boring bar base body