

**Malleable cast iron screw clamp, Jaw capacity: 400mm****Order data**

| | |
|--------------|---------------|
| Order number | 860100 400 |
| GTIN | 4008158014531 |
| Item class | 82C |

Description**Version:**

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. With plastic protective cover on the clamping jaw.

Standard:**DIN 5117****Technical description**

| | |
|---------------------------------|----------|
| Throat | 175 mm |
| Jaw capacity | 400 mm |
| Cross section of the slide rail | 32x10 mm |
| Type of product | Clamp |

