

## Pallet add-on rack, Depth 1100 mm, Height: 5000 mm



### Order data

Order number	991206 5000
GTIN	4058255039203
Item class	960

### Description

#### NOTE: Colour selection possible

#### Version:

**Basic rack** consisting of 2 profile frames each with 4 floor anchors and 2 or 3 cross beam pairs.

**Add-on rack** consisting of 1 profile frame with 4 floor anchors and 2 or 3 cross beam pairs.

Additional storage levels can be found under accessories.

**Cross beams** type LNS 100×50×1.5.

Assembled size of extension rack: 2786 mm

#### Description:

#### Assembled size:

#### Overall length of the rack:

For frame stiles S610-M18 and S625-A18:

Nominal length + number of stiles × 86 mm (for S610-M18)

Nominal length + number of stiles × 110 mm (for S625-A18).

#### Colour:

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

#### Note:

- **On uneven floors we recommend additional shim plates.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

- **Allow at least 100 mm for the foot plates between the frame stiles and walls or parts of the building.**

When fitting cross-beams, make sure that the **outer stiles project at least 500 mm above the topmost storage level**. Within the row of racking, a projection of 100 mm is sufficient.

Colour selection: RAL 5010, 2004

Assembled size add-on rack width: 2786 mm

Compartment width: 2700 mm

Shelf load capacity: 1840 kg

Bay load ( $\geq 3$  bays each with 3 pairs of cross beams per bay): 8650 kg

Frame profile: S610-M18

## Technical description

Depth	1100 mm
Assembled size add-on rack width	2786 mm
Height	5000 mm
Customer assembly	yes
Plug-in assembly	yes
Rack installation	Extension rack
Compartment width	2700 mm
Cross-beam type:	LNS 100×50×1.5
Number of rack stiles	1
Shelf load capacity	1840 kg
Rack access	double-sided
Number of pallet slots per bay	12
Frame profile	S610-M18
Bay load ( $\geq 3$ bays each with 3 pairs of cross beams per bay)	8650 kg
Shelf load capacity / maximum distributed shelf load (on metal)	1840 kg
To take pallets with load capacity	613 kg
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Colour selection	RAL 5010, 2004

Product name attribute	Depth 1100 mm
Type of product	Pallet racking

---

## Accessories

Shims for pallet racking frame Set, 3 pieces	991480
Locking pin for cross beam	991331
Floor anchor for pallet racking frame	991470
Cross beam pair LNS 100×50 Cross-beam length 2700 mm	991337 2700