


Pallet add-on rack, Depth 1100 mm, Height: 4500 mm



Order data

Order number	991216 4500
GTIN	4058255039319
Item class	960

Description

NOTE: Colour selection possible

Version:

Basic rack consisting of 2 profile frames each with 4 floor anchors and 2 or 3 cross beam pairs.

Add-on rack consisting of 1 profile frame with 4 floor anchors and 2 or 3 cross beam pairs.

Additional storage levels can be found under accessories.

Cross beams type LNS 110×50×1.5.

Assembled size of extension rack: 2786 mm

Description:

Assembled size:

Overall length of the rack:

For frame stiles S610-M18 and S625-A18:

Nominal length + number of stiles × 86 mm (for S610-M18)

Nominal length + number of stiles × 110 mm (for S625-A18).

Colour:

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

Note:

- **On uneven floors we recommend additional shim plates.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

- **Allow at least 100 mm for the foot plates between the frame stiles and walls or parts of the building.**

When fitting cross-beams, make sure that the **outer stiles project at least 500 mm above the topmost storage level**. Within the row of racking, a projection of 100 mm is sufficient.

Colour selection: RAL 5010, 2004

Assembled size add-on rack width: 2786 mm

Compartment width: 2700 mm

Shelf load capacity: 2580 kg

Bay load (≥ 3 bays each with 3 pairs of cross beams per bay): 9180 kg

Frame profile: S610-M18

Technical description

Depth	1100 mm
Rack access	double-sided
Rack installation	Extension rack
Height	4500 mm
Number of pallet slots per bay	12
Compartment width	2700 mm
Shelf load capacity	2580 kg
Bay load (≥ 3 bays each with 3 pairs of cross beams per bay)	9180 kg
Plug-in assembly	yes
Frame profile	S610-M18
Customer assembly	yes
Assembled size add-on rack width	2786 mm
Number of rack stiles	1
Cross-beam type:	LNS 100×50×1.5
Shelf load capacity / maximum distributed shelf load (on metal)	2580 kg
To take pallets with load capacity	860 kg
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Colour selection	RAL 5010, 2004

Product name attribute	Depth 1100 mm
Type of product	Pallet racking

Accessories

Floor anchor for pallet racking frame	991470
Shims for pallet racking frame Set, 3 pieces	991480
Locking pin for cross beam	991331