

Pallet basic rack, Depth 1100 mm, Height: 3000 mm



Order data

Order number	991221 3000
GTIN	4058255039340
Item class	960

Description

NOTE: Colour selection possible

Version:

Basic rack consisting of 2 profile frames each with 4 floor anchors and 2 or 3 cross beam pairs.

Add-on rack consisting of 1 profile frame with 4 floor anchors and 2 or 3 cross beam pairs.

Additional storage levels can be found under accessories.

Cross beams type EGN 120×50×1.5.

Assembled size of basic rack: 2872 mm

Description:

Assembled size:

Overall length of the rack:

For frame stiles S610-M18 and S625-A18:

Nominal length + number of stiles × 86 mm (for S610-M18)

Nominal length + number of stiles × 110 mm (for S625-A18).

Colour:

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

Note:

- **On uneven floors we recommend additional shim plates.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

- **Allow at least 100 mm for the foot plates between the frame stiles and walls or parts of the building.**

When fitting cross-beams, make sure that the **outer stiles project at least 500 mm above the topmost storage level**. Within the row of racking, a projection of 100 mm is sufficient.

Colour selection: RAL 5010, 2004

Assembled size basic rack width: 2872 mm

Compartment width: 2700 mm

Shelf load capacity: 3250 kg

Bay load (≥ 3 bays each with 2 pairs of cross beams per bay): 10415 kg

Frame profile: S610-M18

Technical description

Depth	1100 mm
Cross-beam type:	EGN 120×50×1.5
Assembled size basic rack width	2872 mm
Compartment width	2700 mm
Frame profile	S610-M18
Customer assembly	yes
Number of rack stiles	2
Rack access	double-sided
Height	3000 mm
Plug-in assembly	yes
Number of pallet slots per bay	9
Rack installation	Basic rack
Bay load (≥ 3 bays each with 2 pairs of cross beams per bay)	10415 kg
Shelf load capacity	3250 kg
Shelf load capacity / maximum distributed shelf load (on metal)	3250 kg
To take pallets with load capacity	1083 kg
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Colour selection	RAL 5010, 2004

Product name attribute	Depth 1100 mm
Type of product	Pallet racking

Accessories

Locking pin for cross beam	991331
Floor anchor for pallet racking frame	991470
Shims for pallet racking frame Set, 3 pieces	991480