

Pallet add-on rack, Depth 1100 mm, Height: 4000 mm



Order data

| | |
|--------------|---------------|
| Order number | 991226 4000 |
| GTIN | 4058255039425 |
| Item class | 960 |

Description

NOTE: Colour selection possible

Version:

Basic rack consisting of 2 profile frames each with 4 floor anchors and 2 or 3 cross beam pairs.

Add-on rack consisting of 1 profile frame with 4 floor anchors and 2 or 3 cross beam pairs.

Additional storage levels can be found under accessories.

Cross beams type EGN 120×50×1.5.

Assembled size of extension rack: 2786 mm

Description:

Assembled size:

Overall length of the rack:

For frame stiles S610-M18 and S625-A18:

Nominal length + number of stiles × 86 mm (for S610-M18)

Nominal length + number of stiles × 110 mm (for S625-A18).

Colour:

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

Note:

- **On uneven floors we recommend additional shim plates.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

- **Allow at least 100 mm for the foot plates between the frame stiles and walls or parts of the building.**

When fitting cross-beams, make sure that the **outer stiles project at least 500 mm above the topmost storage level**. Within the row of racking, a projection of 100 mm is sufficient.

Colour selection: RAL 5010, 2004

Assembled size add-on rack width: 2786 mm

Compartment width: 2700 mm

Shelf load capacity: 3250 kg

Bay load (≥ 3 bays each with 3 pairs of cross beams per bay): 10250 kg

Frame profile: S610-M18

Technical description

| | |
|--|-----------------|
| Plug-in assembly | yes |
| Frame profile | S610-M18 |
| Rack installation | Extension rack |
| Number of rack stiles | 1 |
| Cross-beam type: | EGN 120×50×1.5 |
| Assembled size add-on rack width | 2786 mm |
| Shelf load capacity | 3250 kg |
| Compartment width | 2700 mm |
| Depth | 1100 mm |
| Bay load (≥ 3 bays each with 3 pairs of cross beams per bay) | 10250 kg |
| Rack access | double-sided |
| Height | 4000 mm |
| Number of pallet slots per bay | 12 |
| Customer assembly | yes |
| Shelf load capacity / maximum distributed shelf load (on metal) | 3250 kg |
| To take pallets with load capacity | 1083 kg |
| Height adjustment interval | 50 mm |
| Type of installation | Plug-in racking |
| Colour selection | RAL 5010, 2004 |

| | |
|------------------------|----------------|
| Product name attribute | Depth 1100 mm |
| Type of product | Pallet racking |

Accessories

| | |
|--|--------|
| Locking pin for cross beam | 991331 |
| Floor anchor for pallet racking frame | 991470 |
| Shims for pallet racking frame Set, 3 pieces | 991480 |