

Pallet add-on rack, Depth 1100 mm, Height: 3000 mm



Order data

Order number	991226 3000
GTIN	4058255039401
Item class	960

Description

Version:

Basic rack consisting of 2 profile frames each with 4 floor anchors and 2 or 3 cross beam pairs.

Add-on rack consisting of 1 profile frame with 4 floor anchors and 2 or 3 cross beam pairs.

Additional storage levels can be found under accessories.

Cross beams type EGN 120×50×1.5.

Assembled size of extension rack: 2786 mm

Description:

Assembled size:

Overall length of the rack:

For frame stiles S610-M18 and S625-A18:

Nominal length + number of stiles × 86 mm (for S610-M18)

Nominal length + number of stiles × 110 mm (for S625-A18).

Colour:

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

Note:

- **On uneven floors we recommend additional shim plates.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**
- **Allow at least 100 mm for the foot plates between the frame stiles and walls or parts of the building.**

When fitting cross-beams, make sure that the **outer stiles project at least 500 mm above the topmost storage level**. Within the row of racking, a projection of 100 mm is sufficient.

Colour selection: RAL 5010, 2004

Assembled size add-on rack width: 2786 mm

Compartment width: 2700 mm

Shelf load capacity: 3250 kg

Bay load (≥ 3 bays each with 2 pairs of cross beams per bay): 10415 kg

Frame profile: S610-M18

Technical description

Customer assembly	yes
Height	3000 mm
Compartment width	2700 mm
Cross-beam type:	EGN 120×50×1.5
Plug-in assembly	yes
Shelf load capacity	3250 kg
Bay load (≥ 3 bays each with 2 pairs of cross beams per bay)	10415 kg
Rack installation	Extension rack
Number of storage level	3
Rack access	double-sided
Number of pallet slots per bay	9
Frame profile	S610-M18
Number of rack stiles	1
Depth	1100 mm
Assembled size add-on rack width	2786 mm
Shelf load capacity / maximum distributed shelf load (on metal)	3250 kg
To take pallets with load capacity	1083 kg
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Colour selection	RAL 5010, 2004

Product name attribute	Depth 1100 mm
Type of product	Pallet racking