

**Toolholder form B6 radial left-hand, long, Shank Ø d1: 30mm****Order data**

Order number	319080 30
GTIN	4045197955029
Item class	32V

Description**Version:**

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

b ₂	65 mm
h ₁	20 mm
h ₅	38 mm
b ₁	100 mm
h ₂	29 mm
l ₁	22 mm

Data sheet

h_6	28 mm
Shank $\varnothing D_1$	30 mm
Colour code for VDI shanks	VDI 30
l_2	40 mm
Shape	B
Type of product	VDI tool arbor